




Dimensions



Model number

WCS3-CS70-L0

Code rail, polyester laminate

Features

- Flexible installation by means of alu profile- or mounting bracket system
- High chemical resistance
- Low weight
- Without fixation holes

Note

laminate version

Technical data

General specifications

Length	0.1 ... 314.5 m
Radius of bend	≥ 300 mm

Ambient conditions

Operating temperature	-40 ... 60 °C (-40 ... 140 °F)
Storage temperature	-40 ... 60 °C (-40 ... 140 °F)
Installation temperature	10 ... 60 °C (50 ... 140 °F)

Mechanical specifications

Material thickness	0.75 ... 0.95 mm
Tension loading	≤ 260 N
Material	polyester laminate
Thermal expansion coefficient	approx. 2.8×10^{-5} / K
Mass	40 g / m

General information

Ordering information	WCS3-CS70-L0: without mounting holes WCS3-CS70-L1: with standard mounting holes WCS3-CS70-L2: with Vahle VKS mounting holes
----------------------	---