



RS422 TO TTY CONVERTER, MALE (9-PIN) TO FEMALE (15-PIN), FOR SCREW CONNECTION TO RS 422 INTERFACE, 180 DGR CABLE OUTLET, FOR CONNECTION OF SIMATIC S5

### Product type designation

### Installation type/mounting

Wall mounting/direct mounting possible

Yes; Can be screwed onto the HMI

### Interfaces

Number of pins HMI-side

9; Pin (RS422)

Number of pins device-side

15; Socket (TTY)

### Standards, approvals, certificates

CE mark

Yes

### Ambient conditions

Ambient temperature in operation

- Min. 0 °C
- max. 55 °C

Storage/transport temperature

- Min. -20 °C
- max. 70 °C

Relative humidity

- Operation, max. 95 %

### Mechanics/material

Screw type

- 4.5 V Yes; HMI page

Type of housing (front)

- plastic Yes

Dimensions	
Width	42 mm
Height	62 mm
Thickness	11 mm

Weights	
Without packaging	28 g

Scope of supply	
Delivery unit in items	1

other	
Note:	suitable for all SIMATIC HMI RS422 interfaces, for details refer to the operating instructions of the respective device

Usable in the following products	
• Product 1	6AV6642-0*
• Product 2	6AV6542-0*
• Product 3	6AV6545-0*
• Product 4	6AV6644-*
• Product 5	6AV6545-8*
• Product 6	6AV6640-0C*
• Product 7	6AV6643-7BA00-*
• Product 8	6AV6643-7CD00-*
• Product 9	6AV6643-7DD00-*
• Product 10	6av2124-0*
• Product 11	6av2124-1*
• Product 12	6AV2124-2*
• Product 13	6AV6647-0*
• Product 14	6AV6643-8*
• Product 15	6AV2123-2*

**last modified:** 12.03.2015