

R222 - Handy Rolls

Handy Roll - Norton R222 - 50mm x25m Gr60

Artical Number: 63642531825

EAN: 3157620183341

SizeDerived: 50mm x25m



Description

R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal and finishing metal.

Features & Benefits

Aluminium oxide abrasive is sharp enough to remove surface material with manual pressure , Versatile aluminium oxide abrasive for hand sanding of wood and metal

Cloth backing provides flexibility for sanding around pipes, contours and curves, can also be torn easily to size , For general purpose maintenance applications and offers extra durability and even wear , For general purpose maintenance applications offers extra durability and even wear

Flexible cotton backing ideal for sanding profiled surfaces and round steel parts , Flexible cotton backing ideal for sanding profiled surfaces and round wooden or steel parts , Resin bond system promotes excellent grain adhesion for applications from deburring to blending and finishing

Dispenser unit for easy storage and product protection

Application Data

Material Application: STEEL, NON-FERROUS, STAINLESS STEEL

Machine: Manual Sanding

Process: Sanding

Equipments:



Technical Data

Marketing CAP:	R222	Length:	25 m
Backing Material:	Light Cotton J wt.	Width:	50 mm
Grit:	60		
Color:	Maroon		
Coated Shape:	Rolls Trimmed		
Coated Sub-Shape:	Handyroll		