


Item no.: 233-512
 Product description: PCB TERMINAL STRIP 2 SOLDER PINS / POLE 12 POLE
 PIN SPACING 2.54 MM / 0.1 IN WITH PUSH BUTTONS



Produkt kann von Bild abweichen / product may differ

Packing unit 140 4*35 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	4.75 g
Color	orange
No. of connection Points	12
No. of potentials	12
pole count	12
Height	15.5 mm
Height	0.61 in
Width	32.78 mm
Width	1.291 in
Depth	13.9 mm
Depth	0.547 in
Pin spacing from	2.54 mm
Pin spacing from	0.1 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A
Pollution degree	2

Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	6 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 0.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 0.5 mm ²
Cross section [mm ²]	0 - 0.25 mm ²
Cross section [mm ²]	0 - 0.25 mm ²
Cross section [AWG]	28 - 20 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
233-512	ABS	04-HG469925/1-PDA	250	4	0,08-0,5
233-512	BV	11915/A0	250	6	0,08-0,5
233-512	CSA	154112-1465035	150	4	28-20
233-512	DNV	E-9215	250	4	0,08-0,5
233-512	GL	17296-00HH	250	4	0,08-0,5
233-512	KEMA	90.6212.01/02	250	6	0,08-0,5
233-512	RMR	11130002	250	4	0,08-0,5
233-512	UR	E45172	150	4	18-28

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected