HellermannTyton

RT40R9C2



Article Number: 115-06219

Releasable Cable Tie, 8.5" Long, 40 lb Tensile Strength, PA66, Natural, 100/pkg

RoHS



Base Data

Local Order Number	RT40R9C2
Туре	RT40R
Color	Natural (NA)
Features and Benefits	 Special design offers a release feature for quick and easy access to wire bundles. Head design provides high tensile strength with very low insertion force even after repeated use. Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Releasable Cable Tie, 8.5" Long, 40 lb Tensile Strength, PA66, Natural, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	40.0 lbs
Minimum Tensile Strength (Metric)	180.0 N
Length L (Imperial)	8.5 "
Length L (Metric)	215.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.16 "
Width W (Metric)	4.0 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	2.0 "
Bundle Diameter Max. (Metric)	51.0 mm
Thickness T (Imperial)	0.05 "
Thickness T (Metric)	1.2 mm

Logistics and Packaging

Carton Quantity 5000 Pieces

Weight (Metric) 1.2 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes

© HellermannTyton 2015