



Main

Product or component type	Uninterruptible power supply (UPS)
Mounting support	Wall Floor
Reset	Automatic reset
Topology	Line interactive

Complementary

Type of installation	Indoor
Surge Energy	156 J
Type of signal	Stepped approximation to a sinewave
Protection device type	Surge protection device (SPD) Miniature circuit breaker (MCB) Fuse
Input voltage	230 V AC
Output voltage	230 V AC
IP degree of protection	IP20
Transfer time	6 ms
Network frequency	45...65 Hz
Power range	650 VA 375 W
Electrical connection	Input: 1 inlet IEC 320 C14 Output: 6 outlet IEC 320 C13
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Battery type	Lead-acid battery
Number of batteries	1
Charging time	8 h
Battery voltage	12 V
Battery life	5 year(s)
Quantity per set	Set of 1
Net weight	4.5 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	92.5 mm
Width	160.5 mm
Depth	305 mm

Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...6561 ft
Ambient air temperature for operation	0...40 °C
Product certifications	CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.5 kg
Package 1 Height	30.505 cm
Package 1 width	16.51 cm
Package 1 Length	9.246 cm
SCC14	10731304338465

Contractual warranty

Warranty	2 years
----------	---------