


DC/AC Inverters, pure sine wave

- 230 V output voltage from 12 or 24 V battery
- Power up TV/Video, appliances, battery chargers (laptop, mobile phones), instruments, tools, and other equipment
- Ideal for industrial and mobile applications, and for caravans, boats, and cars/trucks
- Built-in alarm
- Short circuit proof
- Available in 12 V and 24 V voltage versions
- CE and "E"-marked
- 230 V utgangsspenning fra 12 el. 24 V batteri
- Strøm til TV/video, husholdningsapparat, batteriladere (laptop, mobiltelefon), instrumenter, verktøy og annet utstyr
- Ideelt for profesjonelt og mobilt utstyr og for camping, hytte, båt og bil
- Innebygget alarm
- Kortslutningssikker
- Tilgjengelig i 12 V og 24 V spenningsversjoner
- CE og "E"-merket



Technical specifications	Tekniske data	12 V	24 V
Input voltage:	Inngangsspenning:	10-15 VDC	20-30 VDC
Output voltage:	Utgangsspenning:	230 VAC +5/-10% (50 Hz)	
Output power	Utgangseffekt		
• Continuous:	• Kontinuerlig:	2284: 150 W / 2285: 300 W	
• Intermittent:	• Kortvarig:	2284: 300 W / 2285: 500W	
Temperature range	Temperaturområde		
• Operating:	• Drift:	0° C - 50° C	
No load current:	Tomgangsstrøm:	< 2284:0,5A 2285:0,7A	< 0,4 A
Output wave form:	Kurveform:	Pure sine wave / Ren sinus	
Efficiency:	Effektivitet:	>90%	
Low battery alarm:	Alarm ved lav batterispenning:	10,7 V	21,4 V
Low battery shut-down:	Avbrudd ved lav batterispenning:	10 V	20 V
Electrical safety standard:	Elektrisk sikkerhetsstandard:	EN 60950	
EMC standards	EMC standarder		
• Emission:	• Emisjon:	EN 61000-6-3	
• Immunity:	• Immunitet:	EN 61000-6-1	
Protection:	Sikring:	Input low voltage, input overvoltage, low battery alarm, overtemperature, overload protection and short circuit proof Cooling fan	
		Mot lav inngangsspenning, inngang mot overspenning, alarm ved lav batt. spenning, termisk sikret, overlast beskyttet og kortslutningssikker Kjølevifte	
MTBF:	MTBF:	2284: 63.000 h/ t 2285: 55.000 h/t	
DC terminals:	DC terminaler:	2284: Fixed cable w. battery clips 2285: Fast ledning m. batteriklemmer 2285: Terminal blocks (skrew T) w. battery clips Skruterminaler m. batteriklemmer	
Dimensions (LxWxH):	Mål (LxBxH):	190 x 152 x 66 mm	
Dimensions mounting holes:	Mål monteringshull:	110 x 145mm	
Weight:	Vekt:	2284: 1,15 kg / 2285: 1,55 kg	