


# Surface Spot Heaters



## HPG Series




HPG-3515 shown smaller than actual size.

- ✓ Natural Convection Heating Element
- ✓ Compact Design
- ✓ Self Regulating, Highest Power at Low Ambient Temperature
- ✓ Fixing via Flange with 2 Holes for Screw Mounting (Fastener not Provided)
- ✓ Maximum Heater Temperature 170°C (338°F)
- ✓ One Wing

When the heating of a key component is required, the surface and spot heaters provide the right amount of heat where it is needed. The range of applications for these heaters is almost unlimited. Offering many choices in voltage and power output, the

HPG Series promises to be the correct choice for controlled direct heat. A small footprint combined with versatile mounting options further adds to the adaptability of these heaters.





HPG-3515  
shown smaller  
than actual size.

## Specifications

Model No.	HPG-3315/3325/3375	HPG-3415/3425/3475	HPG-3515/3525/3575
Nominal Power Output at 10°C (50°F)	8W	10W	13W
Electrical Protection Class	II		
Ingress Protection (EN60529)	IP20		
Maximum Body Temperature (25°C Ambient)	170°C (338°F)		
Operating Temperature Range	-30 to 70°C (-22 to 158°F)		
Storage Temperature Range	-40 to 70°C (-40 to 158°F)		
Nominal Input Voltage Heating Element	115 Vac/230 Vac/24 Vdc		
Dimensions (Cross-Section), mm (inch)	28 x 7 (1.10 x 0.28)		
Dimensions (Length), mm (inch)	30 (1.18)	50 (1.97)	60 (2.36)
Lead Wire Type	Silicone AWG20		
Lead Wire Length, mm (inch)	300 mm (11.8")		
Wire Termination	Splice crimp 6 mm (0.24")		
Weight: g (oz)	17 (0.60)	21 (0.74)	29 (1.02)

## To Order Visit [omega.com/hpg](http://omega.com/hpg) for Pricing and Details

Model No.	Description
HPG-3315	8 W, 30 x 28 mm (1.18 x 1.10"), 300 mm (11.8") leads, 115V
HPG-3325	8 W, 30 x 28 mm (1.18 x 1.10"), 300 mm (11.8") leads, 230V
HPG-3375	8 W, 30 x 28 mm (1.18 x 1.10"), 300 mm (11.8") leads, 24V
HPG-3415	10 W, 50 x 28 mm (1.97 x 1.10"), 300 mm (11.8") leads, 115V
HPG-3425	10 W, 50 x 28 mm (1.97 x 1.10"), 300 mm (11.8") leads, 230V
HPG-3475	10 W, 50 x 28 mm (1.97 x 1.10"), 300 mm (11.8") leads, 24V
HPG-3515	13 W, 60 x 28 mm (2.36 x 1.10"), 300 mm (11.8") leads, 115V
HPG-3525	13 W, 60 x 28 mm (2.36 x 1.10"), 300 mm (11.8") leads, 230V
HPG-3575	13 W, 60 x 28 mm (2.36 x 1.10"), 300 mm (11.8") leads, 24V

Comes complete with operator's manual.

Ordering Example: HPG-3315, 8 W, 30 x 28 mm (1.18 x 1.10"), 1 wing, 2 holes, 300 mm (11.8") leads, 115V.