


Category (ETIM):	Mounted luminaire
Type:	stail-SAX LED
Order number:	60322024160
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
Mains voltage:	230V / 50Hz
System performance (W):	69
Luminaire luminous flux (lm):	6500
lm/W:	94
Energy efficiency class:	A+
Certifications:	IP 20, protection class I, BAP 65°<1500, F, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	4.8
Dimensions LxWxDxH (mm):	1240 x 198 x 56
Cable entry KE X/Y (mm):	0 / 50
mounting method:	Surface single mounting, Surface light run mounting, Mounting rail mounting
EAN-number:	4020863309412
Commodity code:	94051098

stail-SAX/1200-2 LED 6500lm 840 • vw • ED • 60322024160




Lighting technology

Micro-parabolic louvre, silky matt-direct distribution
SAX/1200-2 LED 6500 lm 840



Mounted luminaire; Sheet steel housing, flat rectangular cross section, visible installation height 26 mm with 30 mm clearance from the ceiling; end faces made of steel; Housing colour traffic white RAL 9016; Direct light distribution using reflectivity-enhanced parabolic aluminium louvre, silk matt with low installation height cross blades, for workstations, omnidirectional glare reduction according to the current DIN-EN 12464-1 standard, self-engaging. Electrical connection via 3-pole connection terminal with plug-in contacts.

Dimensions LxWxDxH (mm): 1240 x 198 x 56
Cable entry KE X/Y (mm): 0 / 50
Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm): 6500
lm/W: 94
Operating device: Electronic driver (1 pcs.)
System performance (W): 69
Energy efficiency class: A+
Certifications: IP 20, protection class I, BAP 65°<1500, F, Indoor, CE



Regiolux GmbH
Type: stail-SAX/1200-2 LED 6500 840 ET vw
Article number: 60322024160
Product deep link: <http://www.regiolux.de/en/article/60322024160>
5 year guarantee after registration on website.