

Cutting body solid carbide TiAlN for Top Drill M 1

For universal use up to 1300 N/mm²



Application:

High-performance drilling in conjunction with indexable insert drill for universal application up to 1300 N/mm²

Execution:

- Precision-ground indexable insert, tip angle 140°

Advantage:

- Simply replacement of cutting body: No screws or clamps required
- The cutting body can be replaced using a wrench, which is supplied with each tool body
- No regrinding costs
- Consistent performance from cutting edge to cutting edge



| | |
|---------------------------------|--------------------|
| Art. no. | 11224 108 |
| Brand | WIDIA |
| Manufacturer Part Number | 3849059 |
| Cutting material | SC |
| Carbide type | WU25PD |
| Cutting edge diameter | 10.8 mm |
| Indexable insert type | W15 |
| Surface | TiAlN |
| Cutting direction | Right-hand cutting |
| Angle of the tip | 140 Degree |
| Gross Weight | 0.003 kg |
| Product Group | 1XA |

EAN

4021169585180