

Conical drill bit set HSS, uncoated

For universal use up to 1000 N/mm²

ORION[®]

Application:

For producing bores in thin sheets made from steel, non-ferrous metals and cast iron. Also suitable for all plastics, for hard paper and plywood, as well as all materials of similar structure and strength.

Execution:

- Profile-ground to meet the highest requirements for dimensional accuracy and process reliability

Advantage:

- Innovative cutting geometry: All bores are burr and chatter free
- User-friendly regrinding: Drills can be reground repeatedly
- No deformations even with the thinnest material thicknesses
- Robust metal box protects the tool from damage



Art. no.	11403 010
Brand	ORION
Manufacturer Part Number	11403010
Cutting material	HSS
Surface	Uncoated
Tool holding device	Cylinder shank
Composition of set	Type 0/1/2 + drilling paste
Number of pieces in assortment/set	4 PCS
Gross Weight	0.523 kg
Product Group	103

EAN

4039247035267

