

## Depth micrometer

**ORION**<sup>®</sup>

### Application:

For measuring bore depths and shoulders.

### Execution:

- Scale with anti-glare, brushed chromium plated finish
- Steel measuring needles hardened and lapped
- Measuring range per measuring needle: 25 mm
- Advanced friction coupling

### Delivery:

In a case



<b>Art. no.</b>	<b>31630 150</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	31630150
<b>Min./max. length measuring range</b>	0-150 mm
<b>Digit increment</b>	0.01 mm
<b>Measuring surface diameter</b>	4.5 mm
<b>Bridge length</b>	102 mm
<b>Bridge width</b>	17 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Spindle clamping</b>	Yes
<b>Number of measurement needles</b>	6 PCS
<b>DIN</b>	863
<b>Calibration Group</b>	DT
<b>Gross Weight</b>	0.560 kg
<b>Product Group</b>	3BB

### EAN

4053625127160