

Electronic pocket callipers

Digital ABS callipers CoolantProof IP67 with drive roller

Mitutoyo

Application:

For measuring external, internal, step and depth dimensions.

Execution:

- Digimatic
- With drive roller
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- High resistance to water and dust (protection class IP67)
- Survive temporary, complete immersion in water without damage

Delivery:

Delivered in a box



| | |
|---|--|
| Art. no. | 32018 214 |
| Brand | MITUTOYO |
| Manufacturer Part Number | 500-763-20 |
| Min./max. length measuring range | 0-200 mm |
| Min./max. length measuring range in inches | 0-8 in |
| Data transmission type | DIGIMATIC |
| Depth gauge rod | Flat |
| IP protection class | IP 67 |
| With drive wheel | Yes |
| Error limit | 0.001 in |
| Length of jaw | 50 mm |
| Design | Imperial, Metric |
| Digit height | 9 mm |
| Length of cross tips | 20 mm |
| Digit increment | 0.01 mm |
| Digit increment in inches | 0.0005 in |
| Type of locating | With locking screw |
| Preset function | No |
| With mm / inch switching | Yes |
| Length | 290 mm |
| With automatic shut off | Yes |
| Battery designation | 1,5 V SR44 |
| Number of rechargeable batteries/batteries | 1 PCS |
| Weight of rechargeable battery/battery | 0.002 kg |
| Battery voltage | 1.55 V |
| Type of rechargeable battery/battery | Silver oxide |
| Calibration Group | A |
| Functions | Absolute function, Origin (Dimension preset), Automatic switch-off, ABS function |
| Gross Weight | 0.565 kg |
| Product Group | 3MA |

EAN

4946368694023