

Workbench undercounter cabinet with 8 drawers

Height 710 mm, width 570 mm, drawers with full extension

Application:

For the individual assembly of a workbench with workbench panel and base.

Execution:

- Solidly welded steel sheet construction
- Drawers with high-quality Delrin rollers
- Drawers with slots all around for inserting compartment rails and dividers
- Drawers with slotted sheet steel bottom for attaching and fixing individual items
- Drawers flush with cabinet housing, no protruding grip handles
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- Central locking with rotary cylinder security lock, incl. 2 keys
- Suitable insert material for drawers, see no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

| FH mm | KH mm |
|----------|----------|
| 60 | 40 |
| 60 | 40 |
| 60 | 40 |
| 60 | 40 |
| 90 | 70 |
| 90 | 70 |
| 90 | 70 |
| 120 | 100 |



| | |
|--|--------------------------|
| Art. no. | 50212 413 |
| Brand | HK |
| Manufacturer Part Number | 50212413 |
| Number of drawers | 8 PCS |
| Load-carrying capacity per drawer | 70 kg |
| Height | 710 mm |
| Depth | 680 mm |
| Drawer width (inner dimension) | 450 mm |
| Drawer depth (inner dimension) | 600 mm |
| With single pull-out safety brake | Yes |
| Drawer surface | 0.27 m ² |
| With doors | No |
| Drawer with slots | Yes |
| Perforated drawer base | Yes |
| Central locking | Yes |
| Lock type | DOM® locking system |
| Material | Sheet steel |
| Surface | Powder-coated |
| Colour of front | Anthracite grey RAL 7016 |
| Cabinet colour | Light grey RAL 7035 |
| Width | 570 mm |
| Pullout type | Full extension |
| Gross Weight | 82.000 kg |
| Product Group | 5BC |

EAN

4053625402847