


BU-P6883 (Dual 5-Way Binding Post)



- The BU-P6883 is a dual binding post with a standard spacer. The posts are spaced at 0.75" (19mm). Accepts wire up to 12 AWG in through hole, and accepts standard, unshrouded 4mm banana plugs.
- Overall length 1.8" (46mm), overall width 1.4" (36mm), overall height 0.65" (16.5mm)
- Material: Posts Nickel-plated brass
Knobs, Spacers Nylon
- Mounting:
 - Mount thru panels up to 0.25" (6.35mm) thick. Recommended panel cutout is 2X \varnothing 0.465" (11.8mm) holes spaced 0.75" (19.05mm) apart center-to-center.
- Rating: Current 30 Amps
Voltage Hands-free testing at 500V
Temperature -40°C to 80°C