

Precision Milliohm Meter

✓ Portable Milliohm meter provides resolution to 0.1m
Using 4-wire Kelvin clip test leads

Features:

- High accuracy and performance for low resistance measurements
- Large 0.7" (18mm) LCD 1999 count
- Manual zero display adjust
- Overrange indication
- Compact, durable field service housing with protective cover
- Complete with 4-wire cables with Kelvin clip connectors



Specifications	Range	Resolution	Max Voltage	Accuracy ±(%rdg+digits)
Resistance	200m	100μ	3.8VDC	±(0.75%+4d)
	2000m	1m	3.4VDC	±(0.75%+2d)
	20	10m	3.4VDC	±(0.75%+2d)
	200	100m	3.2VDC	±(0.75%+2d)
	2k	1	3.2VDC	±(0.75%+2d)
Power	110VAC, 60Hz or 220VAC 50Hz			
Dimensions	6.3 x 2.8 x 3.4" (160 x 120 x 85mm)			
Weight	1.5lb (680g)			

Ordering Information:

- 380460.....Precision Milliohm Meter, 110VAC
 380460-NIST380460 with Calibration Traceable to NIST
 380462.....Precision Milliohm Meter, 220VAC
 380462-NIST380462 with Calibration Traceable to NIST
 380465.....Spare Kelvin Clip Test Lead Set

