



ENGLISH

Datasheet

Stock No: 123-5034, 123-5035, 123-5036, 123-5037

RS Pro Stainless Steel Cable Ties



Part No	Colour	Material	UL	Maximum Operating Temperature	Type
123-5034	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5035	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5036	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5037	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball

Part No	Maximum Bundle Diameter	Length		Pack Size	Operating Temperature Range	Tensile Strength(factory)
123-5034	50 mm	200 mm	4.6 mm	100	-80 to +538 °C	1112 N
123-5035	102 mm	360 mm	7.9 mm	50	-80 to +538 °C	1559 N
123-5036	25 mm	125 mm	4.6 mm	100	-80 to +538 °C	1112 N
123-5037	102 mm	360 mm	4.6 mm	100	-80 to +538 °C	1112 N