



Specifications:

Electrical	
Rated voltage	300V 250V
Rated current	10A 18A
Wire range	26-12AWG 2.5mm ²
With standing voltage	AC2000V/1Min
Mechanical	
Torque	0.4Nm(3.5Lb-in.)
Ambient temperature	-40°C to 105°C
Strip length	7mm
Dimensions	
Pitch	5.0mm (197in) 7.5mm (295in)
Poles	2P3P-24P
Material	
Housing	PA66, UL94V-0
Screws	M2.5, Steel, Cr ³ Zn plated
Pin header	Brass, Tin plated
Cage	Brass, Ni plated

Ways	Size	Order code
2	7.5mm	21-3017
3		21-3018