



ACRYLIC FIBRES ON REEL 20 M

Fibre optics



Product characteristics

acrylic fibres on a reel

20 m

Connection to fibre optic amplifiers type OBF

Environment

Ambient temperature [°C] -30...70

Mechanical data

Design for types OBF, OOF

Length [mm] 20000

Min. bending radius [mm] 30

Fiber arrangement



Fibre diameter [mm] 1

Outer diameter [mm] 2.2

Fibre optic PMMA; can be cut to length

Sheathing PE (polyethylene)

Weight [kg] 0.339

Remarks

Pack quantity [piece] 1