

## T30XL9M4



**Article Number:** 111-02907

**Standard Cable Tie, 14" Long, 30lb Tensile Strength, PA66, Natural, 1000/pkg**



Download spec sheet

### Base Data

|                              |                                                                                                                                                                                                                                                                                                                                                                                       |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Local Order Number</b>    | T30XL9M4                                                                                                                                                                                                                                                                                                                                                                              |
| <b>Type</b>                  | T30XL                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Color</b>                 | Natural (NA)                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Features and Benefits</b> | <ul style="list-style-type: none"> <li>• Inside serrations allow for strong hold on cables and wire bundles.</li> <li>• Head design provides high tensile strength with very low insertion force.</li> <li>• Bent tail ensures a quick and simple installation.</li> </ul>                                                                                                            |
| <b>Product Description</b>   | HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation. |
| <b>Short Description</b>     | Standard Cable Tie, 14" Long, 30lb Tensile Strength, PA66, Natural, 1000/pkg                                                                                                                                                                                                                                                                                                          |

### Product Dimensions

|                                            |                 |
|--------------------------------------------|-----------------|
| <b>Minimum Tensile Strength (Imperial)</b> | 30.0 lbs        |
| <b>Minimum Tensile Strength (Metric)</b>   | 135.0 N         |
| <b>Length L (Imperial)</b>                 | 14.0 "          |
| <b>Length L (Metric)</b>                   | 365.0 mm        |
| <b>Fixation Method</b>                     | None            |
| <b>Identification Plate Position</b>       | none            |
| <b>Releasable Closure</b>                  | No              |
| <b>Tie Closure</b>                         | plastic pawl    |
| <b>Variant</b>                             | Inside Serrated |
| <b>Width W (Imperial)</b>                  | 0.14 "          |
| <b>Width W (Metric)</b>                    | 3.5 mm          |
| <b>Bundle Diameter Min. (Imperial)</b>     | 0.06 "          |
| <b>Bundle Diameter Min. (Metric)</b>       | 1.5 mm          |
| <b>Bundle Diameter Max. (Imperial)</b>     | 4.13 "          |
| <b>Bundle Diameter Max. (Metric)</b>       | 105 mm          |

### Logistics and Packaging

|                                  |      |
|----------------------------------|------|
| <b>Quantity Per</b>              | bag  |
| <b>Package Quantity (Metric)</b> | 1000 |
| <b>Carton Quantity</b>           | 5000 |

### Material and Specifications

---

|                                      |                                  |
|--------------------------------------|----------------------------------|
| <b>Material</b>                      | Polyamide 6.6 (PA66)             |
| <b>Material Shortcut</b>             | PA66                             |
| <b>Flammability</b>                  | UL94 V2                          |
| <b>Halogenfree</b>                   | Yes                              |
| <b>Operating Temperature</b>         | -40°F to +185°F (-40°C to +85°C) |
| <b>ROHS Compliant</b>                | Yes                              |
| <b>Certification/Specification</b>   | UL-ZODZ2.E64139                  |
| <b>UL Listed (US and Canada)</b>     | Yes                              |
| <b>UL Recognized (US and Canada)</b> | Yes                              |