

Han M23 P Cable to Cable Housing 7-12mm



Part number	09 15 600 0310
Specification	Han M23 P Cable to Cable Housing 7-12mm
HARTING eCatalogue	https://b2b.harting.com/09156000310

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M23 Power
Type of hood/housing	Panel feed through housing
Description of hood/housing	Rear mounting EMC version

Version

Size	M23
------	-----

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	7 ... 12 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	5
Net weight	83.44 g
Country of origin	Germany
Customs tariff number	85366990