

PWLN clamp holder with internal cooling, negative

For copy and longitudinal face turning using WN indexable inserts

ATORN[®]

Application

For copy, longitudinal and face turning with WN indexable insert, 80°.

Version

- precision-made steel carrier with high-performance cooling system, nickel-plated, hardened, adjustable clamping system, type W, attack angle 93°, tip angle 80°, clearance angle 0°

Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable working
- Triple-edge geometry lowers cost per cut
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- adjustable clamp minimises vibrations and ensures good power transmission



Art. no.	17839 720
ISO name	PWLN R/L 2020 K08 IK G1/8
Shaft height	20 mm
Shank width	20 mm
Length	150 mm
Length of head	34 mm
Programming size	32 mm
Suitable for indexable inserts	WN.. 0804..
Tool design	Left
DIN	4983

EAN-Code

4050293566062