

Clamping heads, round version

ORION®

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

Art. no.	22001 282
Brand	ORION
Manufacturer Part Number	22001282
Size	65
Design	Without stem
Profile shape	Round and smooth
Clamping diameter	36 mm
Length	53 mm
Min./max. clamping range diameter	4-65 mm
Gross Weight	1.780 kg
Product Group	2AO



EAN

405362546888 1