

## Steel sack trucks with vertical struts and support brackets

Load capacity 350 kg, pneumatic tyres

**fetra**  
Transportgeräte

### Execution:

- made of tubular steel with steel sheet front shovel
- sturdy welded structure
- Bolt-on and thus interchangeable front shovel
- Height 1,200 mm, total width 620 mm
- Wheels with plastic rims and roller bearings
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant

### Delivery:

disassembled



<b>Art. no.</b>	<b>50270 321</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	B1215L
<b>Design</b>	With bracket for horizontal loading, With vertical bar
<b>Toe plate width</b>	450 mm
<b>Toe plate depth</b>	150 mm
<b>Material</b>	Steel pipe
<b>Material of wheel</b>	Air
<b>Load-carrying capacity</b>	350 kg
<b>Width</b>	620 mm
<b>Height</b>	1200 mm
<b>Colour</b>	Brilliant blue RAL 5007
<b>Total stop optional</b>	No
<b>Wheel diameter</b>	260 mm
<b>Made in</b>	Germany
<b>Ability to climb stairs</b>	No
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	16.000 kg
<b>Product Group</b>	5AB

### EAN

4017976112152