

Large cabinet with easy-view storage bins

Doors with perforated/slotted panels

RasterPlan

Application:

For clearly-arranged storage of small parts in RASTERPLAN easy-view storage bins.

Version:

- Stable steel sheet metal structure with double-walled, warp-resistant hinged doors with inset triple-bolt security cylinder lock, with 2 keys, opening angle more than 200°
- Full-length rod guidance, internal doors equipped with RASTERPLAN perforated slotted panels, double-walled side walls
- Galvanised shelves, adjustable in increments of 10 mm
- Fitted with RASTERPLAN easy-view storage bins made of impact-proof and shock-proof polyethylene, colour coded
- For accessories such as labels, lids see from no. 50638 850-876 in the Workstation chapter.

Delivery:

Without labels



Art. no.	50639 311
Model	11
Door design	Perforated plates/slotted plates
Height	1950 mm
Width	1130 mm
Depth	590 mm
Number of shelves, depth 250 mm	7
Number of shelves, depth 340 mm	3
Number of bins 85 x 105 x 45 mm	32
Number of bins 160 x 105 x 75 mm	70
Number of bins 230 x 140 x 130 mm	28
Number of bins 350 x 200 x 150 mm	20
Load-carrying capacity per shelf	50 kg
Load-carrying capacity per drawer	50 kg
Lock type	Cylinder lock
Material	Sheet steel
Body colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Surface	Plastic-coated

EAN-Code

4251142219317