

## DN7.2 standard steel coupling

in accordance with ISO 6358

**ATORN**<sup>®</sup>

### Version

- check valve in the clutch, forcibly unlocked when coupling. plug without a check valve.
- sliding sleeve to 8 bar, easy to operate with one hand.
- material:
- coupling: steel
- connector: galvanised steel
- seals: NBR
- springs: spring steel
- rollers: Niro steel

### Advantage

- robust and therefore ideal for heavy-duty use



<b>Art. No.</b>	<b>75423 460</b>
<b>Type</b>	with hose nozzle
<b>DN nominal width</b>	DN 7,2
<b>Inner hose diameter</b>	8 mm
<b>Flow capacity</b>	1300 l/min
<b>Max. working pressure</b>	16 bar
<b>Min. working pressure</b>	1 bar
<b>Length</b>	57 mm
<b>Width across flats</b>	21 mm
<b>Min./max. temperature resistance</b>	-10 to 90 °C
<b>Material</b>	Steel

### EAN-Code

4050293533606

