



# Ecoclick Starters

## S10 4-65W SIN 220-240V WH EUR/12X25CT

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

### Product data

General Information	
System Description	Single

  

Operating and Electrical	
Power (Nom)	4 65 W
Pulse Voltage (Min)	900 V
Non Reclosure Voltage (Min)	140 V
Voltage (Nom)	220-240 V

  

System characteristics	
Capacitor	Yes

  

Mechanical and Housing	
Housing Color	White

Cap-Base Information	
Cap-Base Information	2 Pins

  

Product Data	
Full product code	871150069769133
Order product name	S10 4-65W SIN 220-240V WH EUR/12X25CT
EAN/UPC - Product	8711500697691
Order code	928392220230
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	300
Material Nr. (12NC)	928392220230
Net Weight (Piece)	7.000 g

## Ecoclick Starters

### Dimensional drawing

F

Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/12X25CT	40.3 mm	21.5 mm

S10 4-65W SIN 220-240V WH EUR

