



**BE-8010 - BE-8252**

**ERGO™ Slotted Straight Tipped  
Screwdrivers with Rubber Grip  
0.3-1.2 mm x 60-200 mm**



## PRODUCT DETAILS



- Screwdriver developed according to the scientific ERGO™ process
- For slotted head screws
- Phosphate finished tip for higher accuracy
- three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Maximum comfort with minimum effort thanks to an ergonomic design
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- Flat face to prevent rolling away
- Integrated hanging hole
- High-performance alloy steel blade with chrome plating, entirely hardened for high protection against corrosion, long life tool
- Standards: ISO 2380 and DIN 5264



**Follow the Fish!**



## PRODUCT ATTRIBUTES

Product								
<b>BE-8002</b>	0.3 mm	2.0 mm	60 mm	2 mm	17 mm	103 mm	163 mm	30 g
<b>BE-8010</b>	0.4 mm	2.5 mm	60 mm	2.5 mm	17 mm	103 mm	182 mm	31 g
<b>BE-8210</b>	0.4 mm	2.5 mm	75 mm	2.5 mm	17 mm	103 mm	178 mm	33 g
<b>BE-8020</b>	0.5 mm	3.0 mm	60 mm	3 mm	17 mm	103 mm	163 mm	30 g
<b>BE-8020L</b>	0.5 mm	3.0 mm	75 mm	3 mm	17 mm	103 mm	178 mm	33 g
<b>BE-8022</b>	0.5 mm	3.0 mm	100 mm	3 mm	17 mm	103 mm	203 mm	34 g
<b>BE-8220</b>	0.5 mm	3.0 mm	125 mm	3 mm	17 mm	103 mm	228 mm	36 g
<b>BE-8225</b>	0.5 mm	3.0 mm	200 mm	3 mm	17 mm	103 mm	322 mm	45 g
<b>BE-8030</b>	0.6 mm	3.5 mm	75 mm	3.5 mm	17 mm	103 mm	178 mm	34 g
<b>BE-8230</b>	0.6 mm	3.5 mm	125 mm	3.5 mm	17 mm	103 mm	178 mm	37 g
<b>BE-8235</b>	0.6 mm	3.5 mm	200 mm	3.5 mm	20 mm	122 mm	322 mm	45 g
<b>BE-8040</b>	0.8 mm	4.0 mm	100 mm	4 mm	20 mm	122 mm	222 mm	39 g
<b>BE-8240</b>	0.8 mm	4.0 mm	175 mm	4 mm	20 mm	122 mm	297 mm	47 g
<b>BE-8241</b>	1.0 mm	5.5 mm	125 mm	5.5 mm	27 mm	122 mm	247 mm	73 g
<b>BE-8242</b>	1.0 mm	5.5 mm	150 mm	5.5 mm	27 mm	122 mm	272 mm	80 g
<b>BE-8250L</b>	1.0 mm	5.5 mm	200 mm	5.5 mm	27 mm	122 mm	322 mm	90 g
<b>BE-8251</b>	1.0 mm	6.0 mm	150 mm	6 mm	36 mm	122 mm	272 mm	47 g
<b>BE-8252</b>	1.2 mm	6.5 mm	150 mm	6.5 mm	36 mm	122 mm	272 mm	47 g

