



- easy handling
- straight action principle
- ratchet release
- contact positioning with flap locator type FC
- precisely ground profiles
- burnished surface
- ergonomically formed soft grips
- colour: rape yellow/signal black
- fully recyclable; RoHS complied
- application range: FC2 contacts
- wire gauge: profile 1: 0,14-0,32mm<sup>2</sup>
- profile 2: 0,32-0,56mm<sup>2</sup>
- weight approx. 610 g

for FC2 crimp contacts:					
09 06 000 9571	male	2	0,14-0,56	26-20	0,8-2,0
09 06 000 9551	male	1	0,14-0,56	26-20	0,8-2,0
09 06 000 8481	female	2	0,14-0,56	26-20	0,8-2,0
09 06 000 8471	female	1	0,14-0,56	26-20	0,8-2,0
09 06 000 6461	female	Sn	0,14-0,56	26-20	0,8-2,0
contact no.	male / female	PL	wire gauge	AWG	Insulation $\varnothing$

	All rights reserved Department EL PD	All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol.	Ref.
		Created by WAERMKER	Inspected by HAERTLING	Standardisation KOHLER	Date 2020-08-04	State Final Release
Title Crimping Set FC2						Doc-Key / ECM-Nr. 10088504/UGD/000/B 500000177293
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 09990000772		Rev. B	Page 1/1