

PRODUCT SPECIFICATION

USB Standard Charger Model: M452


Revision History

Revision	Date	Initiator	Reason for Change
0.0	20 Mar 2023	CC Li	Initial release

Prepared By	Approved By
CC Li	Vincent Lam
Date: 20 Mar 2023	Date: 20 Mar 2023

GP Batteries

Product Specification



Product Name : USB 4-Slot Charger M452

Input : USB Input from DC5V 1A adaptor or Charging Dock (D451, D851, D461 or D861)

Charging Channels : 4 independent channels ; 1 slot/channel for 1- 4 pcs AA/AAA NiMH batteries

Output Voltage : 1.4V

Input from Adaptor

Charging Current : 1100/1100/730/550mA approx. for charging 1/2/3/4 pcs AA Ni-MH Batteries

730/730/490/370mA approx. for charging 1/2/3/4 pcs AAA Ni-MH Batteries

Charging Time : Approx. 120/120/180/240Min for charging 1/2/3/4 pcs AA 2100mAh Ni-MH Batteries

Approx. 85/85/115/170Min for charging 1/2/3/4 pcs AAA 850mAh Ni-MH Batteries

Model no.: M452

Input from Charging Dock

Charging Current : 1800/1100/730/550mA approx. for charging 1/2/3/4 pcs AA Ni-MH Batteries

1200/730/490/370mA approx. for charging 1/2/3/4 pcs AAA Ni-MH Batteries

Charging Time : Approx. 78/120/180/240Min for charging 1/2/3/4 pcs AA 2100mAh Ni-MH Batteries

Approx. 50/85/115/170Min for charging 1/2/3/4 pcs AAA 850mAh Ni-MH Batteries

Trickle Charging Current : 110/110/73/55mA approx for 1/2/3/4 pcs AA Ni-MH Batteries

73/73/48/36mA approx for 1/2/3/4 pcs AAA Ni-MH Batteries

Standby current at no input: <0.1mA

LED Indication : Green LEDs ON for 0.5 second after just USB power input

Charging in progress - Green LED slow flashing

Fully charged - Green LED ON

Bad/Primary Batteries inserted - Red LED fast flash

Input Voltage (Out of Range <4.5V or >5.5V) – Red and green led alternate flash

Battery Level Check (BLC)* - Green LED ON for Battery Full

Green LED Slow Flash for Battery NOT Full

^{*} Insert 1-4 batteries in slot 1/2/3/4, it will start BLC mode with green LED indication on corresponding channel as mentioned above and keep for 5s. Then will go to normal charging To recheck BLC, just take out and insert battery again.

GP Batteries

Product Specification

Safety protection : 1) Timer protection -3/3/4.5/6 hours for 1/2/3/4 pcs batteries (Adaptor input)

2/3/4.5/6 hours for 1/2/3/4 pcs batteries (Charging Dock input)

Model no.: M452

2) -dv

3) Temperature cut-off

4) Primary battery protection5) Reverse polarity protection

Operation Temperature : 0°C to 33°C for input via charging dock at vertical placement

0°C to 30°C for input via individual adaptor or power bank at horizontal placement

Dimensions : 68 (L) x 78 (W) x 26 (H) mm

Weight : 52 g (approx.)

Certification : CE, UKCA, Rohs, FCC

Warranty Period : 12 months from ex-factory date