

TPC 292411



Sample image

Order symbol : TPC 292411

Product nr : 5824003


Description : Enclosure, PC

Remarks : Grey cover


EAN : 6418074078797

El. number :

- Finland : 3424375
- Denmark : 8212052136



2xM20 knock out



Dimensions :

	Height	Width	Depth
mm :	289	239	107
inch :	11.38	9.41	4.21

Materials :

Material : Polycarbonate

Temperatures :

Temperature °F (continuous) : -40 ... 175

Accessories :

MP 2924	Mounting plate, for enclosures:
DR 215	DIN-35 Mounting rail, for enclosures: (215 x 35 x 1)
DR 265	DIN-35 Mounting rail, for enclosures: (265 x 35 x 1)
FP 10674	Wall fastening lug (2 pcs) incl. screws

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07; IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Certificates :

Certificate FI 40343