

POWER CABLE M8, PREASSEMBLED WITH M8 PLUG AND M8 SOCKET, 4 CORE, LENGTH 1,0M



Figure similar

Product type designation	
General information	
Product description	Flexible cable (4-core), preassembled at each end with a 4-pin M8 male / female connector
Application/function	For connection to ET 200AL for 24 V DC power supply
Degree and class of protection	
Degree of protection to EN 60529	
• IP65	Yes
• IP67	Yes
Ambient conditions	
Ambient temperature during assembly, min.	-30 °C
Ambient temperature during assembly, max.	80 °C
Storage/transport temperature	
• Min.	-40 °C
• max.	80 °C
Cables	
Cable designation	4 Li9Y 0.50
Cable length	1 m
Number of electrical cores	4
Outer diameter of inner conductor	0.8 mm
Outer diameter of core insulation	1.46 mm
Outer diameter of cable sheath	5.2 mm

Number of bending cycles	2 500 000; Cable carrier compliant for 2.5 million bending cycles with a bending radius of 52 mm, a speed of 3 m/s and an acceleration of 10 m/s ²
Permissible bending radius, single bend, min.	26 mm
Permissible bending radius, multiple bends, min.	52 mm
Bending radius for continuous bending	52 mm
Color of cable sheath	gray
Color of core insulation of energy core	white / brown / blue / black
Weight per length	44 kg/km

Mechanics/material

Type of cable outlet	180 degree cable outlet
Material of housing	plastic
Material of core insulation	PP
Material of cable sheath	PVC
Material property silicone-free	Yes

last modified: 17.03.2015