

## Product information

# 25 06 160 T

## Snipe Nose Side Cutting Pliers (Radio Pliers)

DIN ISO 5745 IEC 60900 DIN EN 60900

- Pliers with integrated, insulated tether attachment point for a tool tether
- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	25 06 160 T
EAN	4003773081432
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	155 g
Dimensions	160 x 57 x 26 mm
Standard	DIN ISO 5745 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 2.5 mm
Cutting capacities hard wire (diameter)	Ø 1.6 mm
Jaw thickness (joint) (T1)	9.0 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
Jaw length (L3)	50.0 mm
Head width (W3)	16.5 mm

## Technical details



*technical change and errors excepted*