

# EAO – Your Expert Partner for Human Machine Interfaces

## 84-8510.0020 - Switching element without illumination

### 84-8510.0020 - Switching element without illumination



*Attention: The preview is based on a sample product. This can differ from your current configuration.*

#### Other Attributes

Weight 0.005 kg

#### IP-Rating

Protection degree IP40

#### Connection Method

Terminal Plug 2.8 x 0.8 mm

#### Switching element

Switching system Short-travel element  
Contacts 1 NO  
Switching voltage 42 V AC/DC  
Switching current 0.1 A  
Contact material Gold

# EAO – Your Expert Partner for Human Machine Interfaces

84-8510.0020 - Switching element without illumination

## Wiring diagram



## Additional information

Standard version: Cable length 300 mm with insulated ferrule, plug-in terminal 2.8 x 0.8 mm

Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67)

Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occur, the plugs may become loose

## Legend

Contacts: NO = Normally open