

CAB CAB PC 303018 T



Sample photo

Order symbol: CAB PC 303018 T
Product nbr: 8113040
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020130
EI. number:
 Finland: 3424157
 Electric No. 8212020236
 Denmark:
 Electric No. Italy: 7822025
 Electric No. Sweden: 2539941

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions: Length Width Height **Accessories:**

mm:	300	300	180
inch:	11.8	11.8	7.1

EKIV 27	DIN-35 Mounting rail
DS35270E1	DIN-35 Mounting rail
FP A 33	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 33	Front plate
FP 12-33	Front plate
FP 12x2-33	Front plate
DRF 33	DIN rail frame set

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Smoked grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP65
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960

Accessories:

EKIV 33	Mounting plate
---------	----------------

Certificates:

Germanischer Lloyd (GL)
 SGS Fimko
 Lloyds Register of Shipping (LR)
 Gost R

