



Price\* : 94.87 GBP



## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1FG
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F185 LC1F225
Control circuit type	AC at 60 Hz
[Uc] control circuit voltage	115...120 V AC 60 Hz
Average resistance	2.87 Ohm at 20 °C
Inductance of closed circuit	0.49 H
Operating time	20...35 ms closing 7...15 ms opening
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 55 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.35...0.55 Uc 50/60 Hz (at 55 °C) Operational: 0.85...1.1 Uc 50/60 Hz (at 55 °C)
Inrush power in VA	970 VA 60 Hz cos phi 0.3 (at 20 °C)
Hold-in power consumption in VA	66 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	18...24 W at 60 Hz

## Environment

Ambient air temperature for operation	-5...55 °C
Product weight	0.55 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------