

Product data sheet

Item No. 94.425.6003.7

Cable assembly BST14I2KFB- 50 60GN01

geis® Connection cable female - free end; length: 6m; type BST14I2; 2-pole; 50 V / 3 A; colour of coding: grün with black strain-relief; cable: FB-2Y(ST)Y2x2x0,8, colour: grün



Item No.	94.425.6003.7
EAN	4015573460003
Order Unit	20 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	3 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	2
Mechanical coding	Yes
Interlockable	No
Color of coding/ contact carrier	Green
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	2
Nominal cross section conductor	0.5 mm ²
Degree of protection (IP)	IP20
Wire strip length	9 mm
sheath strip length	21 mm
Preparation of conductor ends	Other
Cable type	FB-2Y(ST)Y 2x2x0.8

Cable colour	Green
Cable diameter	6.1 mm
Version of cable	Female - free end

Material

Surface finish	Gilt
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	6 m
--------------	-----