

Proficlean safety spray gun

Hose nozzle for internal hose diameter 12.5 mm



Application:

For cleaning or washing machines and parts in machining areas using water or drilling fluid.

Art. no.	75202 021
Model	Proficlean
Min./max. flow capacity	4-10 l/min
Max. operating pressure	20 bar
Connection thread	G 1/2 inch
Nozzle size	2 mm
Min./max. temperature conditions	+5 to +90 °C
Weight	0.7 kg

EAN-Code

4030875147773

