



Model. UFH2TN

UPRIGHT FAN HEATER 2000W WITH THERMOSTATIC CONTROL

Features & Benefits

- Modern colour coordinated White body to suit all decors
- Constructed from flame retardant material with Neon power indicator light and integrated carrying handle
- Selection Settings: Normal (Cool Air), Warm (1000W) or Hot (2000W) for instant heat
- Thermal link protected to increase element life expectancy

Safety Information

IMPORTANT - Before undertaking any work on or maintenance of fitting:-

- Switch off power supply and allow sufficient time to cool before handling
- Do not dispose of decommissioned fitting in household waste
- Dispose of fitting in the appropriate section of your local civic amenity site or recycling centre only

Product Summary

The Airmaster space heating range begins with 2kW upright or floor Fan heaters plus three Convector options – with thermostat, turbo fan or timer. A full package of Oil filled radiators follows, with power levels from 0.5kW to 2.5kW, including a 2kW timer option. Panel heaters come with 1.0kW, 1.5kW or 2.0kW ratings with features including a slim, compact and light design, silent operation, an instant flow of heat and LCD timer and temperature controls.

Technical Specifications

General Information	
Product Colour/Finish	White
Dimensions (mm)	(H)250 x (W)215 x (D)130
Ingress Protection (IP)	n/a
Electrical	
Input Voltage (V)	220-240V
Output Rating (W)	2000W
Frequency (Hz)	50Hz
Working temperature (°C)	n/a
Mounting Position	Floor Standing
Mounting Bracket (Y/N)	N
Cable	1.7Mtr 2 Core Cable with BS1362 approved plug
Class	I
Approvals	BS EN60335-1:2012, CE, GS, RoHS
Energy Rating (ErP)	n/a
Performance Data	
Air Volume/Velocity (cbm)	n/a
Noise level (dB)	Floor Standing
Tip-Over Sensor (Y/N)	N
Over-Heat protection (Y/N)	Y
Construction	
Body	Die-Cast PC
Grill	Integrated PC Grills
Motor	No motor
Nett Weight	1.0Kg
Gross Weight	1.2Kg
Warranty Period (Years)	1Yr
Other	
Applications	Domestic and commercial applications