

97 52 63 DG Four-Mandrel Crimping Pliers for turned contacts



- Technical details
- Description
- Special

	No.	97 52 63 DG	
	EAN	4003773063209	
	Pliers	chrome plated	
	Handles	with multi-component grips	
	Applications	turned contacts	
	Capacity	0,08 - 2,5	mm ²
	AWG	28 - 13	
	Number of crimping positions	1	
	Length	195	mm
	Net weight	388	g

- for crimping turned contacts
- four-mandrel crimping for top-quality crimping connections
- mandrel gauge to check the basic setting
- repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- high operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

Model:

- crimping capacity can be adjusted in increments of 0.01 mm
- with digital display of the preset crimping capacities and possibility of re-calibration via RESET function with electronic wear monitoring
- adjustment in mm, inches or comparable selection positions according to MIL
- pliers in a plastic case with foam insert and standard locator for precise positioning of the contacts

Turned contacts are used for particularly demanding plug-type connections, e.g. in medical industry and aeronautics. Extremely reliable crimping connections can be achieved only with pliers that work with absolute precision and maintain the required crimping depth in the 1/100 mm range.

technical change and errors excepted