

AS Adapter AT/AGT

Spezifikation

Adapter zur Spannungsversorgung aller AS LED-Elemente von Einbau-Ø8 mm bis Ø16 mm.

Achtung:

Adapter nur mit montiertem Leuchtelement betreiben!

Material

Gehäuse: PC grau

Stromaufnahme

15 mA bei 60V
7 mA bei 130V
5 mA bei 230V

Anschluss

Flachstecker 2,8x0,8 mm

Masse-Anschluß mit rückseitiger Lasche nur bei den Typen AT1 / AT2 / AT4

Optionen

Weitere Betriebsspannungen auf Anfrage möglich



AS Adapter AT/AGT

Specification

Adapter for power supply of all AS LED elements, ranging from mounting-Ø8 mm to Ø16 mm.

Attention:

Adapter only operate with mounted lighting element!

Material

housing: PC grey

Current consumption

15 mA up at 60V
7 mA up at 130V
5 mA up at 230V


Connection

Tab terminal 2.8x0.8 mm

Ground connection with clip on the rear side only at types AT1 / AT2 / AT4

Options

Further operation voltages possible on request



Typ / type	Artikel Nr.: / part number						
	6V	12/14V	24/28V	48V	60V	130V	230V
Schutzdiode DC (AC) Protection diode DC (AC)	AT1	AT2	AT4	AT5	AT6		
Gleichrichter AC/DC Rectifier AC/DC			AGT4			AGT7	AGT8