

ALU KARABINER / ALU KARABINERS




SCHRAUBKARABINER / SCREW KARABINERS

Zum Öffnen werden laut Norm mindestens 3 Umdrehungen benötigt.

According approval you need at least 3 turns for opening.

1 BSK 30 kN EN 362B 3860017

72,4 x 116 mm



BALL-LOCK-KARABINER

Spezielle Form des Twist-Lock-Karabiners
Special form of the twist lock karabiner

9 Ball-Lock 28 kN EN 362B 3860026

63,5 x 111,5 mm

TWIST-LOCK-KARABINERS

BEST. NR. / ART. NO.

2-Weg-Sicherung: Drehen - Öffnen / Two-way-protection: twist - open

2	HMS	22 kN	EN 362B	3860020
3	HMS AA	24 kN	EN 362B, EN 12275B	3860049
4	2-lock DMM	32 kN	EN 362B, EN 12275B	3860047



77 x 123 mm



70 x 110 mm



65,5 x 114 mm

KARABINER MIT DREHWIRBEL / KARABINERS WITH SWIVEL PIVOT

... verhindern Seilkrangel / ... avoid twist in rope


10	AHK	22 kN	EN 362T	3860028
11	3-lock DMM	25 kN	EN 362T	3860040
12	3-lock ISC	27 kN	EN 362T	3860042



71 x 190 mm



70 x 200 mm



73 x 172 mm

TRIPLE-LOCK-KARABINERS

BEST. NR. / ART. NO.

Drei-Weg-Sicherung: Hochschieben - Drehen - Öffnen
Three-way-protection: push up - twist - open

5	OMNI-Triact	20 kN	EN 362B, EN 12275	3860056
6	Oval	22 kN	EN 362B	3860027
7	HMS	24 kN	EN 362B, EN 12275	3860011
8	Harness	22 kN	EN 362A	3860043



71 x 99 mm



61 x 110 mm



70 x 110 mm



71 x 122 mm


SONDERKARABINER / SPECIAL KARABINERS

BEST. NR. / ART. NO.

13	AHK	25 kN	EN 362T, EN 12275K	3860021
14	AHK 3-lock	27 kN	EN 362T	3860041
15	EHK	25 kN	EN 362A+T	3860048
16	Micro	22 kN	EN 12275	3860014
17	RH 60	22 kN	EN 362A	3859107
18	RH120		EN 795	3851020



71 x 141 mm




72 x 140 mm



68 x 134 mm



56 x 94 mm



134 x 235 mm



210 x 500 mm

Weitere Karabiner auf Anfrage.
Other karabiners on request.