Product Specification PDF



Date	Correct as of 14th Aug 2019
Brand	C.K
Product	T4814 25
Description	HDComfort Stubby Screwdriver 6.5mm
Barcode	5013969589009
Commodity code	8205400000
Country of origin	DE



Features & Benefits ~ Shatter resistant acetate handle ~ wipe clean, oil & acid resistant ~ Large square shape handle design for

maximum torque ~ Handle injection moulded directly to blade giving the ultimate bond for increased reliability & durability ~ Anti roll flats to prevent the screwdriver rolling off sloping surfaces ~ Chrome plated toughened alloy steel blade for increased strength & durability ~ Precision machined tip for an exact screw fit & damage free screwdriving ~ Drop forged blades from Chrome Vanadium/Molybdenum steel, hardened and tempered ~ According to DIN 5264, ISO 2380-2 ~ Blade width: 6,5 mm ~ Visible blade length: 25 mm ~ Overall length: 85

mm

Applicable Standards ISO 238 -2
Health & Safety None applicable

Warranty C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures					
	Product only	Product & primary packaging	Secondary packaging	Transit packaging	
Item Quantity	1	1	6	180	
Width mm	31	31	80	350	
Depth mm	31	31	200	300	
Height mm	85	85	50	250	
Weight	56	56	385	12.3	
Packaging Information	Card use	0	Box	Case	
	Card gms	0	49	600	
	Plastic use	0	0	-	
	Plastic gms	0	0	0	
	Metal use	0	0	-	
	Metal gms	0	0	0	
	Timber use	0	0	-	
	Timber gms	0	0	0	