

Part number

CX 20 CF



Brief description:

female insert, 20 poles, crimp connections, 16A 500V, 6kV, 3, 2 modules, modular units series MIXO

Product description		Approvals / Standards	
Model	female insert	Reference standard	EN 61984:2009-06
Version	Crimp connection	Quality mark	DNV-GL, EAC
Product type	for female contacts 16A	Conformity	CQC, CE
Family	MIXO series, customizable inserts	General ordering information	
Size	2 modules	EAN13 code	8015747163880
N. of poles	20 poles	Tariff number	85369095
Technical data		Packaging Information	
Current	16 A (A.C. and D.C.)	Packaging length	350,00 mm
Voltage	500 V	Packaging height	105,00 mm
Rated impulse withstand voltage	6 kV	Packaging width	145,00 mm
Pollution degree	3	Packaging weight	1,61 kg
Operating temperature range (min, max)	-40°C ... +125°C	Packaging volume	5,33 dm ³
IP degree of protection	IP20 without enclosure, IP65/IP66/IP68/IP69 with enclosure	Packaging description	Carton box
Further technical details		Packaging quantity	60 Pcs
Characteristics according to EN 61984	16A 500V 6kV 3; 16A 830V 8kV 2	Packaging EAN code	8015747221061
Insulation resistance	≥ 10 GΩ	Sub-packaging length	35,00 mm
Rated voltage according to UL/CSA	600V	Sub-packaging height	40,00 mm
UL 94 flammability rating	V-0	Sub-packaging width	155,00 mm
Weight	22,00 g	Sub-packaging weight	0,13 kg
		Sub-packaging volume	0,22 dm ³
		Sub-packaging description	Carton tray
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747163903



Part number

CX 20 CF



Catalogue drawings

Catalogue drawings



Notes

the modular inserts must be installed in suitable frames which in turn are installed in traditional housings or COB panel support