

NYS231LBG

3 pole 3.5 mm plug, with large cable outlet, black metal handle with gold plated contacts



Technical Information

Product

Title NYS231LBG

Electrical

Dielectric strength	0.5 kVdc
Insulation resistance	$\geq 1 \text{ G}\Omega$
Rated current	depends on mated connector
Contact resistance	depends on mated connector

Mechanical

Cable O.D.	6 mm
Lifetime	1000 mating cycles

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C