


Number of contacts

# 6-64



Low-profile male header, straight press-in pins


Identification      No. of contacts      Part No.      Drawing      Dimensions in mm

Low-profile male header with straight press-in terminations  
Length: 5.5 mm


No. of contacts	Part No.	Drawing
6	09 18 506	329
10	09 18 510	329
14	09 18 514	329
16	09 18 516	329
20	09 18 520	329
26	09 18 526	329
34	09 18 534	329
40	09 18 540	329
50	09 18 550	329
60	09 18 560	329
64	09 18 564	329

No. of contacts	A	B	E
6	15.2	12.78	2.54 x 2 = 5.08
10	20.3	17.86	2.54 x 4 = 10.16
14	25.4	22.94	2.54 x 6 = 15.24
16	27.9	25.48	2.54 x 7 = 17.78
20	33.0	30.56	2.54 x 9 = 22.86
26	40.6	38.18	2.54 x 12 = 30.48
34	50.8	48.34	2.54 x 16 = 40.64
40	58.4	55.96	2.54 x 19 = 48.26
50	71.3	68.66	2.54 x 24 = 60.96
60	84.0	81.36	2.54 x 29 = 73.66
64	89.1	86.44	2.54 x 31 = 78.74

Marking No. 1 contact




No. 2 contact




No. 1 contact

No. 2 contact



Board drillings

For Performance Level 3 please specify digit  
For Performance Level 2 please specify digit  
S4 = 0.76 μm (30 μinch) Au or PdNi equivalent



Not normally kept in stock

- 1) No polarization slot for 6, 10 or 14 way
- 2) No polarization slot for 6 way
- 3) Pitch tolerance: ± 0.1