

PNOZ m EF 1MM

772170



Configurable control system PNOZmulti 2 expansion module safe monitoring of 1 axis.

Technical details

Approvals:	CE;cULus Listed;TÜV;BG
Number of incremental encoder inputs:	1
Signal level range (Vss):	0,5 - 30,0
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	111.0 mm
Gross weight:	100 g
Net weight:	90 g
Ambient temperature:	0 - 60 °C

Accessories



783542

Spring terminals PNOZ mmcxp, 1 pc.



793542

Screw terminals PNOZ mmcxp, 1 pc.

Optional accessories



773845

PNOZ msi b4 Box



773870

PNOZ msi S09



773871

PNOZ msi S15



773872

PNOZ msi S025



779260

PNOZ mm0.xp connector left (10 pcs)



772201

MM A MINI-IO CAB99 2.5m



772202

MM A MINI-IO CAB99 5.0m



772200

MM A MINI-IO CAB99 1.5m