

Specifications:

Impedance (Ω)	$64 \pm 15\%$ at 1000 Hz at 1.0 V
Rated Power (W)	0.1
Max Power (W)	0.2
Resonance Freq F_o (Hz)	$430 \pm 20\%$ at 1.0 V
Frequency Range (Hz)	$F_o \sim 20000$
Output S.P.L. (dB)	88 ± 3 at .1w/.1m 1.0k, 1.2k, 1.5k, 2.0kHz 78 ± 3 at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHz
Frame Material	ABS UL94 1/16"HB High Heat (BLACK)
Operating Temp	-20 to 55°C
Weight (g)	4.5
Options	For other options contact factory

Dimensions: ± 0.3 (units: mm)

ROHS Compliant

