

## Die, HSSE MF right, pre-slotted and 2 thread chamfer for universal use up to 1300 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For cutting fine metric threads externally in the material groups of steel, stainless steel, non-ferrous metals and special alloys up to a strength of 1300 N/mm<sup>2</sup>.

### Execution:

- right die. tol. 6 g with spiral point, nitrided, pre-slotted and 2.0 pitch

### Advantage:

- standard geometry with excellent price/performance ratio



<b>Art. no.</b>	<b>13447 120</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	13447 120
<b>Thread type</b>	Metric fine thread
<b>Cutting material</b>	HSSE
<b>Tolerance of dies</b>	6 g
<b>Thread type x nominal diameter</b>	MF12
<b>Pitch</b>	1 mm
<b>Outer diameter</b>	38 mm
<b>Height</b>	10 mm
<b>Cutting direction</b>	Right-hand cutting
<b>Gross Weight</b>	0.100 kg
<b>Product Group</b>	1DC

### EAN

4039247074006