

Precision indicator

ATORN®

Application

For measuring lengths. Ideal for measuring instruments and flatness and straightness measurements

Version

- Shock resistant
- Precision-guided measuring pin
- Connection for wire lifter
- Pointer fine adjustment
- Adjustable tolerance marks
- Measuring mechanism on ruby bearings
- suitable for internal precision measuring instruments

Delivery

in case



Art. No.	33163 015
Calibration Group	K
Scale value	0.01 mm
Length measuring range	0.5 mm
Shaft diameter	8 mm
Shaft length	18 mm
Error limit	12 µm
With free stroke	Yes
Measurement force	1 N
Reversal error	3 µm
IP protection class	IP 40
Repeat accuracy	3 µm
DIN	879

EAN-Code

4050293353242

